



Electric Autoclave for sterilisation



THREE DIFFERENT CONTROL SYSTEMS:



**CONTROL BY PRESSURE WITH ATMOSPHERIC PURGE:
MICROCLAVE 2 - MEDICLAVE 12**



**MICROPROCESSOR CONTROL OF TEMPERATURE AND STERILISATION CYCLE,
ATMOSPHERIC AIR PURGE:
PRESOCLAVE II 30 (mod. vertical)
PRESOCLAVE II 50 (mod. vertical)
PRESOCLAVE II 75 (mod. vertical)**



**MICROPROCESSOR CONTROL OF TEMPERATURE AND STERILISATION CYCLE,
PULSED VACUUM AIR PURGE:**

AUTESTER ST DRY PV-B 12 (mod. horizontal)
AUTESTER ST DRY PV-B 18 (mod. horizontal)
AUTESTER ST DRY PV-B 25 (mod. horizontal)

AUTESTER ST DRY PV-II 30 (mod. vertical)
AUTESTER ST DRY PV-II 50 (mod. vertical)
AUTESTER ST DRY PV-II 75 (mod. vertical)
AUTESTER ST DRY PV-II 140 (mod. vertical)



SUMMARY TABLE OF MODEL RANGE

QUICK OVERVIEW

MODELS	Part No.	System DRY	Capacity litres	Temperature °C	Pressure bar	Power W	Control	Purge control	Type
MICROCLAVE 2	4001404	NO	7	121 and 127	1 and 1.5	1000	Pressure thermostat	Atmospheric	Vertical bench top
MEDICLAVE 12	4047725	NO	12	121 and 134	1 and 2	1800	Pressure thermostat	Atmospheric	Vertical bench top
PRESOCLAVE II 30	4002135	NO	30	115 to 134	0.62 to 2	2800	Electronic controller	Atmospheric	Vertical
PRESOCLAVE II 50	4001725	NO	50	115 to 134	0.62 to 2	3600	Electronic controller	Atmospheric	Vertical
PRESOCLAVE II 75	4002136	NO	75	115 to 134	0.62 to 2	3600	Electronic controller	Atmospheric	Vertical
AUTESTER ST DRY PV-B 12	4001727	YES	12	121 and 134	1 and 2	1800	Microprocesador	Purged vacuum	Horizontal bench top
AUTESTER ST DRY PV-B 18	4001728	YES	18	121 and 134	1 and 2	1800	Microprocesador	Purged vacuum	Horizontal bench top
AUTESTER ST DRY PV-B 25	4002414	YES	25	105-121 and 134	0.21-1 and 2	2510	Microprocesador	Purged vacuum	Horizontal bench top
AUTESTER ST DRY PV-II 30	4002514	YES	30	105 to 134	0.21 to 2	2800	Microprocesador	Purged vacuum	Vertical
AUTESTER ST DRY PV-II 50	4002515	YES	50	105 to 134	0.21 to 2	3600	Microprocesador	Purged vacuum	Vertical
AUTESTER ST DRY PV-II 75	4002425	YES	75	105 to 134	0.21 to 2	3600	Microprocesador	Purged vacuum	Vertical
AUTESTER ST DRY PV-II 140	4002426	YES	140	105 to 134	0.21 to 2	7500	Microprocesador	Purged vacuum	Vertical